

UNILIFT CC/KP RANGE MULTI-PURPOSE DRAINAGE PUMPS



UNILIFT KP

UNILIFT CC

The UNILIFT CC/KP range comprises of lightweight yet highly efficient drainage pumps, designed for pumping domestic drain water and grey wastewater.

The submersible single-stage pumps have semi-open impellers that allow particles of $\text{\O}10$ to pass freely while a stainless steel strainer prevents anything bigger to enter the pump. Suitable for both permanent and temporary installation the UNILIFT CC and KP are flexible drainage pumps, ideal for both urgent and recurring drainage installations.

BENEFITS

- Lightweight
- Permanent as well as portable installation
- Simple installation
- Service-friendly
- Optional automatic operation
- High grade stainless steel suitable for light aggressive liquids

APPLICATIONS


- Rainwater, drainage water and water from flooding
- Pool water
- Effluents from showers, washing machines and sinks below sewer level
- Comes in a high grade stainless steel suitable for light aggressive liquids

THE UNILIFT CC/KP RANGE IN MORE DETAIL

UNILIFT CC – KEY FEATURES

- Pumping down to a level of 3 mm above floor
- Prevention of backflow
- Thermal overload protection
- Handy and easy to transport
- Self-venting valve
- Auto-restart
- Connectivity to different outlets via adaptor

UNILIFT CC – PERFORMANCE CURVE




UNILIFT KP – KEY FEATURES

- Prevention of backflow*
- Thermal overload protection
- Auto-restart
- Handy and easy to transport
- Can be supplied with or without a level switch
- Clip-on strainer for easy maintenance
- Optional non return valve to prevent backflow

*Prevention of backflow requires KP fitted with non-return valve

UNILIFT KP – PERFORMANCE CURVE



UNILIFT CC – RANGE


Pump type	Dimensions [mm]			Weight [kg]
	H1	B1	B2	
UNILIFT CC 5	305	160	26.5	4.35
UNILIFT CC 7	305	160	26.5	4.6
UNILIFT CC 9	340	160	26.5	6.5

UNILIFT KP – RANGE

Pump type	Dimensions [mm]			Weight [kg]
	H1	B1	B2	
UNILIFT KP 150	220	140	30	7.3
UNILIFT KP 250	220	140	30	7.0
UNILIFT KP 350	230	140	30	8.1

UNILIFT CC – TECHNICAL DATA

- Max. flow rate, Q: 14 m³/h
- Max. head, H: 9 m
- Liquid temp.: 0 °C to +40 °C
- Max. particle size: Ø10
- Material: Composite
- Low suction to 3 mm



UNILIFT KP – TECHNICAL DATA

- Max. flow rate, Q: 14 m³/h
- Max. head, H: 9 m
- Liquid temp.: 0 °C to +50 °C
- Max. particle size: Ø10
- Material: Stainless steel

